

# AHP2T30J02-024 Cut Sheet



AchieVe IEC limit switch, one-way horizontal lever with 12.5mm plastic roller, 90-degree adjustable head, (2) N.C. contact(s), snap action, with reset, 20-22mm hole spacing, plastic, (2) PG11 and (1) 1/2in NPT cable entries.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AHP2T30J02-024>

## Technical Specifications

|                              |   |
|------------------------------|---|
| <b>Brand</b>                 | AchieVe   |
| <b>Item</b>                  | Limit switch  |
| <b>Switch Type</b>           | IEC   |
| <b>Actuator Type</b>         | One-way horizontal lever with 12.5mm plastic roller |
| <b>Head Type</b>             | 90-degree adjustable                                |
| <b>Contact Type</b>          | (2) N.C.  |
| <b>Action</b>                | Snap action   |
| <b>Reset</b>                 | Yes   |
| <b>Body Width</b>            | 30.3mm  |
| <b>Mounting Hole Spacing</b> | 20-22mm   |
| <b>Material</b>              | Plastic   |
| <b>IP Rating</b>             | IP65  |
| <b>Operating Temperature</b> | -25 to 70 deg C                                     |
| <b>Connection</b>            | (2) PG11 and (1) 1/2in NPT cable entries            |
| <b>Halogen Free</b>          | No  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | NKCR.E191072                           |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |