

AJB-10 Cut Sheet



NITRA pneumatic air jet base, 1in length, brass, #10-32 female threaded.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AJB-10>

Technical Specifications

| | |
|------------------------------|------------------------|
| Brand | NITRA |
| Item | Pneumatic Air jet base |
| Length | 1in |
| Material | Brass |
| Connection | #10-32 female threaded |
| Pressure Range | 0-125 psi |
| Operating Temperature | -20 to 160 degrees F |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |