

# AJB-15 Cut Sheet

NITRA pneumatic air jet base, 1.5in length, brass, #10-32 female threaded.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AJB-15>

---

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Pneumatic Air jet base
<b>Length</b>	1.5in
<b>Material</b>	Brass
<b>Connection</b>	#10-32 female threaded
<b>Pressure Range</b>	0-125 psi
<b>Operating Temperature</b>	-20 to 160 degrees F

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>