

# AJN16-1 Cut Sheet

NITRA pneumatic air jet nozzle, 1in length, straight, brass.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AJN16-1>

---

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Pneumatic Air jet nozzle
<b>Length</b>	1in
<b>Shape</b>	Straight
<b>Flow Coefficient</b>	0.1
<b>Material</b>	Brass
<b>Pressure Range</b>	0-125 psi
<b>Operating Temperature</b>	-20 to 160 degrees F

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>