

AJN16-2 Cut Sheet

NITRA pneumatic air jet nozzle, 2in length, straight, brass.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AJN16-2>

Technical Specifications

Brand	NITRA
Item	Pneumatic Air jet nozzle
Length	2in
Shape	Straight
Flow Coefficient	0.1
Material	Brass
Pressure Range	0-125 psi
Operating Temperature	-20 to 160 degrees F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document