

AJNV-M10N Cut Sheet



NITRA pneumatic air jet needle valve, brass, #10-32 female threaded.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AJNV-M10N>

Technical Specifications

Brand	NITRA
Item	Pneumatic Air jet needle valve
Material	Brass
Connection	#10-32 female threaded
Pressure Range	0-125 psi
Operating Temperature	-20 to 160 degrees F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document