

AJPB-14 Cut Sheet

NITRA pneumatic air jet base, 1.1in length, brass, 1/4in push-to-connect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AJPB-14>

Technical Specifications

Brand	NITRA
Item	Pneumatic Air jet base
Length	1.1in
Material	Brass
Connection	1/4in push-to-connect
Pressure Range	0-125 psi
Operating Temperature	-20 to 160 degrees F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document