

# AM6-AN-4H Cut Sheet



Micro Detectors inductive proximity sensor, tubular, 12mm diameter x 52.5mm body, nickel-plated brass housing, NPN, N.O. output, 8mm sensing distance, non-flush, 2 kHz switching frequency, IP67, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AM6-AN-4H>

## Technical Specifications

|                         |                             |
|-------------------------|-----------------------------|
| <b>Brand</b>            | Micro Detectors             |
| <b>Item</b>             | Proximity sensor            |
| <b>Sensor Type</b>      | Inductive                   |
| <b>Application</b>      | Standard duty               |
| <b>Shape</b>            | Tubular                     |
| <b>Housing Size</b>     | 12mm diameter x 52.5mm body |
| <b>Housing Material</b> | Nickel-plated brass         |
| <b>Barrel Type</b>      | Threaded                    |
| <b>Sensing Method</b>   | Extended sensing            |
| <b>Adjustable</b>       | No                          |
| <b>Number of Wires</b>  | 3                           |
| <b>Switching Output</b> | NPN                         |
| <b>Operation Mode</b>   | N.O. output                 |

|                               |                            |
|-------------------------------|----------------------------|
| <b>Sensing Distance</b>       | 8mm                        |
| <b>Mounting Type</b>          | Non-flush                  |
| <b>IO-Link Compatible</b>     | No                         |
| <b>Switching Frequency</b>    | 2 kHz                      |
| <b>Operating Voltage</b>      | 10-30 VDC                  |
| <b>Operating Temperature</b>  | -25 to 70c                 |
| <b>Weld Field Immune</b>      | No                         |
| <b>Chip Immune</b>            | No                         |
| <b>IP Rating</b>              | IP67                       |
| <b>Connection</b>             | 4-pin M12 quick-disconnect |
| <b>Includes</b>               | Mounting hardware          |
| <b>Additional Information</b> | Purchase cable separately  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E130644                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |