

# AP2R11W02 Cut Sheet



Comepi safety limit switch, stainless steel plunger, (2) N.C. safety output(s), slow action, plastic, (1) PG11 cable entry with 1/2in NPT adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AP2R11W02>

## Technical Specifications

Brand	Comepi
Item	Safety limit switch
Switch Type	IEC
Actuator Type	Stainless steel plunger
Head Type	90-degree adjustable
Safety Output Type	(2) N.C.
Action	Slow action
Reset	Yes
Body Width	30mm
Material	Plastic
IP Rating	IP65
Connection	(1) PG11 cable entry with 1/2in NPT adapter

## Agency Approvals

UL Listed File #	e189258
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	176294
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/AP2R11W02.pdf>  
See store item page for other formats.