

AP2R31W02 Cut Sheet



Comepi safety limit switch, one-way horizontal lever with nylon roller, (2) N.C. safety output(s), slow action, plastic, (1) PG11 cable entry with 1/2in NPT adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AP2R31W02>

Technical Specifications

Brand	Comepi
Item	Safety limit switch
Switch Type	IEC
Actuator Type	One-way horizontal lever with nylon roller
Head Type	90-degree adjustable
Safety Output Type	(2) N.C.
Action	Slow action
Reset	Yes
Body Width	30mm
Material	Plastic
IP Rating	IP65
Connection	(1) PG11 cable entry with 1/2in NPT adapter

Agency Approvals

UL Listed File #	e189258
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	176294
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AP2R31W02.pdf>
See store item page for other formats.