

AP2R31X11 Cut Sheet



Comepi safety limit switch, one-way horizontal lever with nylon roller, (1) N.C. safety output(s), (1) N.O. monitoring output(s), slow action break before make, plastic, (1) PG11 cable entry with 1/2in NPT adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AP2R31X11>

Technical Specifications

Brand	Comepi
Item	Safety limit switch
Switch Type	IEC
Actuator Type	One-way horizontal lever with nylon roller
Head Type	90-degree adjustable
Safety Output Type	(1) N.C.
Monitoring Output Type	(1) N.O.
Action	Slow action break before make
Reset	Yes
Body Width	30mm
Material	Plastic
IP Rating	IP65
Connection	(1) PG11 cable entry with 1/2in NPT adapter

Agency Approvals

UL Listed File #	e189258
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	176294
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AP2R31X11.pdf>
See store item page for other formats.