

# AP2R32W02 Cut Sheet



Comepi safety limit switch, one-way vertical lever with nylon roller, (2) N.C. safety output(s), slow action, plastic, (1) PG11 cable entry with 1/2in NPT adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AP2R32W02>

## Technical Specifications

<b>Brand</b>	Comepi
<b>Item</b>	Safety limit switch
<b>Switch Type</b>	IEC
<b>Actuator Type</b>	One-way vertical lever with nylon roller
<b>Head Type</b>	90-degree adjustable
<b>Safety Output Type</b>	(2) N.C.
<b>Action</b>	Slow action
<b>Reset</b>	Yes
<b>Body Width</b>	30mm
<b>Material</b>	Plastic
<b>IP Rating</b>	IP65
<b>Connection</b>	(1) PG11 cable entry with 1/2in NPT adapter

## Agency Approvals

<b>UL Listed File #</b>	e189258
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	176294
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>