

APDB-112-350-1 Cut Sheet



Penn-Union open power distribution block, finger-safe, 310A, 1-pole, line side: 1 openings accept 350 MCM to 6 AWG Cu/AL, load side: 12 openings accept 4 AWG to 14 AWG Cu/AL, DIN rail or panel mount, UL 1953 listed.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/APDB-112-350-1>

Technical Specifications

| | |
|----------------------------|--------------------------|
| Brand | Penn-Union |
| Item | Power distribution block |
| Terminal Block Type | Open |
| Modular | Yes |
| Finger-safe | Yes |
| Amperage Rating | 310A |
| Number of Poles | 1 |

| | |
|-------------------------------|--|
| Line Side Openings | 1 openings accept 350 MCM to 6 AWG Cu/AL |
| Load Side Openings | 12 openings accept 4 AWG to 14 AWG Cu/AL |
| Mounting | DIN rail or panel |
| SCCR Rating | 100kA SCCR |
| UL Rating | UL 1953 listed |
| IP Rating | IP20 |
| Additional Information | Suitable for branch and feeder circuits |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E534364 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/APDB-112-350-1.pdf>
See store item page for other formats.