

APS-25 Cut Sheet



Minerallac multifunction clip, package of 25. For use with #12 wire, 1/4 rod, 3/8in rod, flanges 1/8 to 3/8in, #10-24 and 1/4in-20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/APS-25>

Technical Specifications

Brand	Minerallac
Item	Multifunction clip
Mounting Holes	#10-24 UNC, 1/4-20 UNC and 1/4in
Material	Spring steel
Finish	Zinc phosphate plated
Minimum Flange Thickness	1/8in
Maximum Flange Thickness	3/8in
UL Type	UL 1565
Quantity per Pack	25
For Use With	#12 wire, 1/4 rod, 3/8in rod, flanges 1/8 to 3/8in, #10-24 and 1/4in-20

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document