

APSKC1-25 Cut Sheet



Minerallac multifunction clip conduit hanger assembly, spring clip, back mount, 25 lbs. Package of 25. For use with 1/8 to 3/8in flanges, #12 wire, 1/4 or 3/8in rod and 1in conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/APSKC1-25>

Technical Specifications

Brand	Minerallac	Rigid Metallic Conduit (RMC) Trade Size	1in
Item	Conduit hanger assembly	Electrical Metallic Tubing (EMT) Trade Size	1in
Mount Type	Multifunction clip	Intermediate Metallic Conduit (IMC) Trade Size	1in
Hanger Type	Spring clip	Reduced Wall Flexible Metal Conduit Trade Size	3/4in
Mount Side	Back	Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1in
Material	Spring steel	Quantity per Pack	25
Finish	Zinc phosphate plated	For Use With	1/8 to 3/8in flanges, #12 wire, 1/4 or 3/8in rod and 1in conduit
Mounting Holes	#10-24 UNC and 1/4-20 UNC		
Minimum Flange Thickness	1/8in		
Maximum Flange Thickness	3/8in		
Load Rating	25 lbs		
Outside Diameter	1.11in-1.31in		

Agency Approvals

CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document