

AR-1C-120A-TL Cut Sheet



ProSense alternating relay, socket mount, finger-safe, 120 VAC coil voltage, SPDT, (1) N.O., (1) N.C., 10A contact rating, 8-pin, LED indicator(s). Relay becomes UL listed when used with 70169-D relay socket.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR-1C-120A-TL>

Technical Specifications

Brand	ProSense
Item	Relay
Relay Type	Alternating
Mounting	Socket
Relay Housing Type	Finger-safe
Coil Voltage	120 VAC
Relay Configuration	SPDT
Output Type	(1) N.O., (1) N.C.
Contact Rating	10A
Connector Type	8-pin
Indicator	LED
Additional Information	Relay becomes UL listed when used with 70169-D relay socket

Agency Approvals

UL Listed File #	E191059
UL Recognized File #	E191059
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR45565
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AR-1C-120A-TL.pdf>
See store item page for other formats.