

# AR-222 Cut Sheet



NITRA pneumatic regulator, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), 4-57 psi adjustable range. For use with Ax-22 series air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR-222>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Regulator
<b>Working Fluid</b>	Air or inert gas
<b>Inlet Port</b>	1/4in female NPT
<b>Outlet Port</b>	1/4in female NPT
<b>Pressure Range</b>	4-57 psi adjustable
<b>Flow Coefficient</b>	0.97
<b>For Use With</b>	Ax-22 series air prep components
<b>Includes</b>	Integral pressure gauge, locking adjustment knob and mounting bracket

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/AR-222.pdf>  
See store item page for other formats.