

AR-322 Cut Sheet



NITRA pneumatic regulator, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), 4-57 psi adjustable range. For use with Ax-32 series air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR-322>

Technical Specifications

Brand	NITRA
Item	Regulator
Working Fluid	Air or inert gas
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Pressure Range	4-57 psi adjustable
Flow Coefficient	3.2
For Use With	Ax-32 series air prep components
Includes	Integral pressure gauge, locking adjustment knob and mounting bracket

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AR-322.pdf>
See store item page for other formats.