

# AR16V0L-12E3R Cut Sheet



Fuji Electric emergency stop pushbutton, IP65, 16mm, push to lock, pull or turn to reset, LED illuminated, (1) N.O./(2) N.C. contact(s), plastic base, plastic bezel, black, Operator: red, mushroom, 32mm, mushroom, plastic, 24 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR16V0L-12E3R>

## Technical Specifications

|                           |                                     |
|---------------------------|-------------------------------------|
| <b>Brand</b>              | Fuji Electric                       |
| <b>Item</b>               | Emergency stop pushbutton           |
| <b>IP Rating</b>          | IP65                                |
| <b>Barrel Size</b>        | 16mm                                |
| <b>Action</b>             | Push to lock, pull or turn to reset |
| <b>Bulb Type</b>          | LED illuminated                     |
| <b>Contact Type</b>       | (1) N.O./(2) N.C.                   |
| <b>Base Material</b>      | Plastic                             |
| <b>Bezel Material</b>     | Plastic                             |
| <b>Bezel Color</b>        | Black                               |
| <b>Operator Color</b>     | Red                                 |
| <b>Operator Type</b>      | Mushroom                            |
| <b>Operator Size</b>      | 32mm                                |
| <b>Operator Shape</b>     | Mushroom                            |
| <b>Operator Material</b>  | Plastic                             |
| <b>Operator Legend</b>    | Arrow                               |
| <b>Voltage Rating</b>     | 24 VAC/VDC                          |
| <b>Voltage Regulation</b> | Full voltage                        |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E44592                                 |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |