

# AR2-332 Cut Sheet



NITRA pneumatic regulator, 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), 7-60 psi range. For use with Ax-33 series air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR2-332>

---

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Regulator
<b>Working Fluid</b>	Pneumatic
<b>Inlet Port</b>	3/8in female NPT
<b>Outlet Port</b>	3/8in female NPT
<b>Pressure Range</b>	7-60 psi
<b>For Use With</b>	Ax-33 series air prep components
<b>Includes</b>	Integral pressure gauge and locking adjustment knob and mounting bracket

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>