

AR2-332 Cut Sheet



NITRA pneumatic regulator, 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), 7-60 psi range. For use with Ax-33 series air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR2-332>

Technical Specifications

Brand	NITRA
Item	Regulator
Working Fluid	Air or inert gas
Inlet Port	3/8in female NPT
Outlet Port	3/8in female NPT
Pressure Range	7-60 psi
For Use With	Ax-33 series air prep components
Includes	Integral pressure gauge and locking adjustment knob and mounting bracket

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AR2-332.pdf>
See store item page for other formats.