

AR22PL-010L3YZA Cut Sheet



Fuji Electric selector switch, 22mm, 2-position, spring return from right, LED illuminated, (1) N.O. contact(s), plastic base, metal bezel, Operator: yellow, knob, 30mm, round, plastic, 115-127 VAC, transformer.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR22PL-010L3YZA>

Technical Specifications

| | |
|---------------------|--------------------------|
| Brand | Fuji Electric |
| Item | Selector switch |
| Barrel Size | 22mm |
| IP Rating | IP65 |
| Number Of Positions | 2 |
| Action | Spring return from right |
| Bulb Type | LED illuminated |
| Contact Type | (1) N.O. |
| Base Material | Plastic |

| | |
|--------------------|-------------|
| Bezel Material | Metal |
| Operator Color | Yellow |
| Operator Type | Knob |
| Operator Size | 30mm |
| Operator Shape | Round |
| Operator Material | Plastic |
| Voltage Rating | 115-127 VAC |
| Voltage Regulation | Transformer |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E44592 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR20479 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AR22PL-010L3YZA.pdf>
See store item page for other formats.