

AR22PL-311L3RZA Cut Sheet



Fuji Electric selector switch, 22mm, 3-position, maintained, LED illuminated, (1) N.O./(1) N.C. contact(s), plastic base, metal bezel, Operator: red, knob, 30mm, round, plastic, 115-127 VAC, transformer.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR22PL-311L3RZA>

Technical Specifications

Brand	Fuji Electric
Item	Selector switch
Barrel Size	22mm
IP Rating	IP65
Number Of Positions	3
Action	Maintained
Bulb Type	LED illuminated
Contact Type	(1) N.O./(1) N.C.
Base Material	Plastic

Bezel Material	Metal
Operator Color	Red
Operator Type	Knob
Operator Size	30mm
Operator Shape	Round
Operator Material	Plastic
Voltage Rating	115-127 VAC
Voltage Regulation	Transformer

Agency Approvals

UL Listed File #	E44592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR20479
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AR22PL-311L3RZA.pdf>
See store item page for other formats.