

# AR30G2L-10L3GZC Cut Sheet



Fuji Electric pushbutton, 30mm, momentary, LED illuminated, (1) N.O. contact(s), plastic base, metal bezel, guarded, Operator: green, extended, 35mm, round, plastic, 115-127 VAC, transformer.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR30G2L-10L3GZC>

## Technical Specifications

<b>Brand</b>	Fuji Electric
<b>Item</b>	Pushbutton
<b>IP Rating</b>	IP65
<b>Barrel Size</b>	30mm
<b>Action</b>	Momentary
<b>Bulb Type</b>	LED illuminated
<b>Contact Type</b>	(1) N.O.
<b>Base Material</b>	Plastic
<b>Bezel Material</b>	Metal

<b>Operator Protection</b>	Guarded
<b>Operator Color</b>	Green
<b>Operator Type</b>	Extended
<b>Operator Size</b>	35mm
<b>Operator Shape</b>	Round
<b>Operator Material</b>	Plastic
<b>Voltage Rating</b>	115-127 VAC
<b>Voltage Regulation</b>	Transformer

## Agency Approvals

<b>UL Listed File #</b>	E44592
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LR20479
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/AR30G2L-10L3GZC.pdf>  
See store item page for other formats.