

# AR30PL-210E3AZC Cut Sheet



Fuji Electric selector switch, 30mm, 2-position, maintained, LED illuminated, (1) N.O. contact(s), plastic base, metal bezel, Operator: orange, knob, 35mm, round, plastic, 24 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR30PL-210E3AZC>

## Technical Specifications

|                     |                 |
|---------------------|-----------------|
| Brand               | Fuji Electric   |
| Item                | Selector switch |
| Barrel Size         | 30mm            |
| IP Rating           | IP65            |
| Number Of Positions | 2               |
| Action              | Maintained      |
| Bulb Type           | LED illuminated |
| Contact Type        | (1) N.O.        |
| Base Material       | Plastic         |

|                    |              |
|--------------------|--------------|
| Bezel Material     | Metal        |
| Operator Color     | Orange       |
| Operator Type      | Knob         |
| Operator Size      | 35mm         |
| Operator Shape     | Round        |
| Operator Material  | Plastic      |
| Voltage Rating     | 24 VAC/VDC   |
| Voltage Regulation | Full voltage |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | E44592                                 |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | LR20479                                |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/AR30PL-210E3AZC.pdf>  
See store item page for other formats.