

# AR30PR-120BZC Cut Sheet



Fuji Electric selector switch, 30mm, 3-position, spring return from left and right to center, (2) N.O. contact(s), plastic base, metal bezel, Operator: black, knob, 35mm, round, plastic.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR30PR-120BZC>

## Technical Specifications

|                            |   |
|----------------------------|---|
| <b>Brand</b>               | Fuji Electric                               |
| <b>Item</b>                | Selector switch                             |
| <b>Barrel Size</b>         | 30mm  |
| <b>IP Rating</b>           | IP65  |
| <b>Number Of Positions</b> | 3   |
| <b>Action</b>              | Spring return from left and right to center |
| <b>Contact Type</b>        | (2) N.O.                                    |
| <b>Base Material</b>       | Plastic                                     |
| <b>Bezel Material</b>      | Metal                                       |
| <b>Operator Color</b>      | Black                                       |
| <b>Operator Type</b>       | Knob  |
| <b>Operator Size</b>       | 35mm  |
| <b>Operator Shape</b>      | Round                                       |
| <b>Operator Material</b>   | Plastic                                     |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E44592                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | LR20479                                |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |