

AR30Q7L-11L3RZC Cut Sheet



Fuji Electric pushbutton, 30mm, push-pull/momentary, LED illuminated, (1) N.O./(1) N.C. contact(s), plastic base, metal bezel, Operator: red, mushroom, 35mm, round, plastic, 115-127 VAC, transformer.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR30Q7L-11L3RZC>

Technical Specifications

Brand	Fuji Electric
Item	Pushbutton
IP Rating	IP65
Barrel Size	30mm
Action	Push-pull/momentary
Bulb Type	LED illuminated
Contact Type	(1) N.O./(1) N.C.
Base Material	Plastic
Bezel Material	Metal

Operator Color	Red
Operator Type	Mushroom
Operator Size	35mm
Operator Shape	Round
Operator Material	Plastic
Voltage Rating	115-127 VAC
Voltage Regulation	Transformer
Includes	(2) N.C. contacts

Agency Approvals

UL Listed File #	E44592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR20479
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AR30Q7L-11L3RZC.pdf>
See store item page for other formats.