

AR30VPL-12EAR Cut Sheet



Fuji Electric emergency stop pushbutton, IP65, 30mm, push to lock, turn to reset, interlocked LED illuminated, (1) N.O./ (2) N.C. contact(s), plastic base, metal bezel, silver, Operator: red, mushroom, 44mm, mushroom, plastic, 24 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR30VPL-12EAR>

Technical Specifications

Brand	Fuji Electric
Item	Emergency stop pushbutton
IP Rating	IP65
Barrel Size	30mm
Action	Push to lock, turn to reset
Bulb Type	Interlocked LED illuminated
Contact Type	(1) N.O./ (2) N.C.
Base Material	Plastic
Bezel Material	Metal

Bezel Color	Silver
Operator Color	Red
Operator Type	Mushroom
Operator Size	44mm
Operator Shape	Mushroom
Operator Material	Plastic
Operator Legend	Arrow
Voltage Rating	24 VAC/VDC
Voltage Regulation	Full voltage

Agency Approvals

UL Listed File #	E44592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/AR30VPL-12EAR.pdf>
See store item page for other formats.