

# AR30WR-010BZC Cut Sheet



Fuji Electric selector switch, 30mm, 2-position, spring return from right, (1) N.O. contact(s), plastic base, metal bezel, Operator: black, lever, 35mm, round, plastic.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AR30WR-010BZC>

## Technical Specifications

Brand	Fuji Electric
Item	Selector switch
Barrel Size	30mm
IP Rating	IP65
Number Of Positions	2
Action	Spring return from right
Contact Type	(1) N.O.
Base Material	Plastic
Bezel Material	Metal
Operator Color	Black
Operator Type	Lever
Operator Size	35mm
Operator Shape	Round
Operator Material	Plastic

## Agency Approvals

UL Listed File #	E44592
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	LR20479
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/AR30WR-010BZC.pdf>  
See store item page for other formats.