

ARD-CM1000AC Cut Sheet



ARDENT clamp meter, AC/DC voltage, AC current, resistance, capacitance, frequency and temperature, 1000A, CAT IV 600V/CAT III 1000V.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ARD-CM1000AC>

Technical Specifications

Brand	ARDENT
Item	Clamp meter
Multimeter Type	Autoranging
Safety Rating	CAT IV 600V/CAT III 1000V
AC Voltage Range	0-3.000 VAC, 0-30.00 VAC, 0-300.0 VAC and 0-1000 VAC
DC Voltage Range	0-30.00 mVDC, 0-300.0 mVDC, 0-3.000 VDC, 0-30.00 VDC, 0-300.0 VDC and 0-1000 VDC
AC Current Range	0.2-1000.0A
Resistance Range	0-30.00 ohm, 0-300.0 ohm, 0-3.000 kohm, 0-30.00 kohm, 0-300.0 kohm, 0-3.000 Mohm and 0-30.00 Mohm
Capacitance Range	0-30.00 nF, 0-300.0 nF, 0-3.000 μ F and 0-30.00 μ F
Frequency Range	0-300.0 Hz, 0-3.000 kHz, 0-30.00 kHz and 0-100.0 kHz

Non-Contact AC Voltage Detection	No
True RMS	No
Diode Tester	Yes
Duty Cycle	2.0-98.0%
Temperature Range	-328 deg F to 1562 deg F and -200 deg C to 850 deg C
Continuity	<40 ohm
Includes	Carrying case, normal tip probe set, alligator clip set, instruction manual, test certificate and 9V battery
Applicable Standards	CE, cULus, IEC 61326: Class B, IEC 61000-4-2, IEC 61000-4-3, IEC 61010-1-2001 and IEC 60529
IP Rating	IP20
Application	Electrical testing

Agency Approvals

UL Listed File #	E546108
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document