

ARD-CMP1000ACDC Cut Sheet



ARDENT clamp meter, AC/DC voltage, AC/DC current, power, resistance and temperature, 1000A, CAT IV 600V/CAT III 1000V.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ARD-CMP1000ACDC>

Technical Specifications

Brand	ARDENT
Item	Clamp meter
Multimeter Type	Autoranging
Safety Rating	CAT IV 600V/CAT III 1000V
AC Voltage Range	0-999.0 VAC
DC Voltage Range	0-999.9 VDC
AC Current Range	0-999.9A
DC Current Range	0-999.9A
Low-Pass Filter (LPF) Current Range	0 to 999.9A DC
Active Power Range	0-9.999 kW, 0-99.99 kW, 0-999.9 kW and 0-9999 kW
Reactive Power Range	0-9.999 kVA _r , 0-99.99 kVA _r , 0-999.9 kVA _r and 0-9999 kVA _r
Apparent Power Range	0-9.999 kVA, 0-99.99 kVA, 0-999.9 kVA and 0-9999 kVA

Horsepower Range	0-9.999 hp, 0-99.99 hp, 0-999.9 hp, 0-9999 hp
kWh Range	0-9.999 kWh, 0-99.99 kWh, 0-999.9 kWh and 0-9999 kWh
Resistance Range	0-9999 ohm
Non-Contact AC Voltage Detection	Yes
True RMS	No
Diode Tester	Yes
Continuity	<40 ohm
Includes	Carrying case, normal tip probe set, alligator clip set, instruction manual, test certificate and 9V battery
Applicable Standards	CE, IEC 61326: Class B, IEC 61326: 2012, IEC 61000-4-2, IEC 61000-4-3 and IEC 61010-1-2010
IP Rating	IP20
Application	Electrical testing and power monitoring

Agency Approvals

CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document