

ARD-MM410 Cut Sheet



ARDENT multimeter, AC/DC voltage, AC/DC current, resistance, continuity, capacitance, frequency and temperature, 10A, CAT III 600V/CAT II 1000V.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ARD-MM410>

Technical Specifications

Brand	ARDENT	Non-Contact AC Voltage Detection	No
Item	Multimeter	True RMS	No
Multimeter Type	Autoranging	Diode Tester	Yes
Safety Rating	CAT III 600V/CAT II 1000V	Duty Cycle	2.0-98.0%
AC Voltage Range	0-400.0 mVAC, 0-4.000 VAC, 0-40.00 VAC, 0-400.0 VAC and 0-1000 VAC	Temperature Range	32 deg F to 2372 deg F and 0 deg C to 1300 deg C
DC Voltage Range	0-400.0 mVDC, 0-4.000 VDC, 0-40.00 VDC, 0-400.0 VDC and 0-1000 VDC	Continuity	<75 ohm
AC Current Range	0-40.00 mA, 0-400.0 mA and 0-10.00A	Includes	(2) fuses (1.6A and 16A), rubber holster, fine tip probe set, instruction manual, test certificate, battery (2 X 1.5V AA) and carrying strap (belt)
DC Current Range	0-40.00 mA, 0-400.0 mA and 0-10.00A	Applicable Standards	CE
Resistance Range	0-400.0 ohm, 0-4.000 kohm, 0-40.00 kohm, 0-400.0 kohm, 0-4.000 Mohm and 0-40.00 Mohm	IP Rating	IP20
Capacitance Range	0-5.00 nF, 0-50.00 nF, 0-500.0 nF, 0-5.000 µF, 0-50.00 µF and 0-200.0 µF	Application	Electrical testing and continuity testing
Frequency Range	0-10.00 Hz, 0-100.0 Hz, 0-1.00 kHz, 0-10.00 kHz, 0-100.0 kHz and 0-500.0 kHz		

Agency Approvals

CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document