

# ASD-33-120A Cut Sheet



NITRA soft start valve, 3-port (3-way), 2-position, single solenoid spring return, N.C., 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), 3/8in female NPT exhaust(s), Cv=15, 120 VAC operating voltage. For use with Ax-33 series air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ASD-33-120A>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Valve
<b>Working Fluid</b>	Air
<b>Valve Type</b>	Soft start
<b>Action</b>	Single solenoid spring return
<b>Port Quantity</b>	3-port (3-way)
<b>Number Of Positions</b>	2
<b>Valve Configuration</b>	N.C.
<b>Inlet Port</b>	3/8in female NPT

<b>Outlet Port</b>	3/8in female NPT
<b>Exhaust Port</b>	3/8in female NPT
<b>Flow Coefficient</b>	15
<b>Operating Voltage</b>	120 VAC
<b>Electrical Connection</b>	DIN style wiring connector
<b>Indicating Type</b>	LED indication
<b>For Use With</b>	Ax-33 series air prep components
<b>Includes</b>	T-bracket

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/ASD-33-120A.pdf>  
See store item page for other formats.