

ASD-33-24D Cut Sheet



NITRA soft start valve, 3-port (3-way), 2-position, single solenoid spring return, N.C., 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), 3/8in female NPT exhaust(s), Cv=15, 24 VDC operating voltage. For use with Ax-33 series air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ASD-33-24D>

Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air
Valve Type	Soft start
Action	Single solenoid spring return
Port Quantity	3-port (3-way)
Number Of Positions	2
Valve Configuration	N.C.
Inlet Port	3/8in female NPT
Outlet Port	3/8in female NPT
Exhaust Port	3/8in female NPT
Flow Coefficient	15
Operating Voltage	24 VDC
Electrical Connection	DIN style wiring connector
Indicating Type	LED indication
For Use With	Ax-33 series air prep components
Includes	T-bracket

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document