

ATLA-11-100 Cut Sheet



Electri-Flex Liquatite liquid-tight flexible metallic conduit, hot dipped galvanized steel, PVC jacket, 1/2in trade size, gray, UL-360 Listed, 100ft/30.4m coil length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ATLA-11-100>

Technical Specifications

Brand	Electri-Flex	Coil Length	100ft/30.4m
Series	Liquatite	UL Rating	UL-360 Listed
Item	Conduit	Operating Temperature	-67 deg F to 221 deg F (-55 deg C to 105 deg C)
Conduit Type	Liquid-tight flexible metallic conduit (LFMC)	UV Resistant	Yes
Liquid-tight	Yes	Applicable Standards	• ANSI/UL-360
Inner Core Material	Hot dipped galvanized steel		• CSA C22.2 No 56-17 Annex A Heavy duty
Outer Material	PVC jacket		• IEC 61386
Trade Size	1/2in	Application	• CEC CSA 22.1-18
Color	Gray		Extreme hot and cold

Agency Approvals

UL Listed File #	E29278
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LL18858
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document