

ATLA-15-50 Cut Sheet



Electri-Flex Liqueflex liquid-tight flexible metallic conduit, hot dipped galvanized steel, PVC jacket, 1-1/2in trade size, gray, UL-360 Listed, 50ft/15.2m coil length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ATLA-15-50>

Technical Specifications

Brand	Electri-Flex	Coil Length	50ft/15.2m
Series	Liquatite	UL Rating	UL-360 Listed
Item	Conduit	Operating Temperature	-67 deg F to 221 deg F (-55 deg C to 105 deg C)
Conduit Type	Liquid-tight flexible metallic conduit (LFMC)	UV Resistant	Yes
Liquid-tight	Yes	Applicable Standards	<ul style="list-style-type: none">• ANSI/UL-360• CSA C22.2 No 56-17 Annex A Heavy duty• IEC 61386• CEC CSA 22.1-18
Inner Core Material	Hot dipped galvanized steel		
Outer Material	PVC jacket		
Trade Size	1-1/2in	Application	Extreme hot and cold
Color	Gray		

Agency Approvals

UL Listed File #	E29278
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LL18858
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document