

ATM1500T Cut Sheet



ATLAS touch screen industrial display, 15in color TFT LCD, analog resistive, 1024 x 768 pixel, XGA, LED backlight, (1) VGA input, (1) serial and (1) USB B port.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ATM1500T>

Technical Specifications

Brand	ATLAS
Item	Industrial display
Touch Screen	Yes
Display Size	15in
Viewable Size	15in
Display Type	Color TFT LCD
Widescreen	No
Display Maximum Colors	16M colors
Display Resolution	1024 x 768 pixel
Display Video Standard	XGA
Touch Panel Type	Analog resistive
Brightness	250nits
Display Orientation	Landscape
Backlight Type	LED
External Power Requirement	100-240 VAC
Housing Rating	NEMA 4/4X/12
Environmental Requirements	Indoor use only
IP Rating	IP65
Mounting	Panel
A/V Port and Connection Type(s)	(1) VGA input (DB15HD female)
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (1) RS-232 (DB9 female)• (1) USB B

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	E200031
RoHS Status	No
EU REACH	View EU REACH document