

AV2-UND/ODER-PS-TS Cut Sheet



di-soric T-coupler patch cable signal converter, (2) 3-pin M8 axial female to 3-pin M8 axial male, AND/OR, 10–35 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AV2-UND/ODER-PS-TS>

Technical Specifications

Brand	di-soric
Item	Signal converter
Form Factor	T-coupler patch cable
Connector Type	(2) 3-pin M8 axial female to 3-pin M8 axial male
Function	AND/OR
Operating Voltage	10–35 VDC
Operating Temperature	-20 to +70 °C
Material	Plastic

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/AV2-UND_ODER-PS-TS.pdf
See store item page for other formats.