

AVS-5271-HL Cut Sheet



NITRA pneumatic manual valve, 5-port (4-way), 2-position, 90 deg hand lever, spring return, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), 1/8in female NPT exhaust(s), Cv=0.78, panel or surface mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AVS-5271-HL>

Technical Specifications

| | |
|---------------------|----------------------------|
| Brand | NITRA |
| Item | Valve |
| Working Fluid | Air or inert gas |
| Valve Type | Manual directional control |
| Port Quantity | 5-port (4-way) |
| Number Of Positions | 2 |
| Operator Type | 90 deg hand lever |
| Action | Spring return |
| Body Material | Aluminum alloy |
| Mounting | Panel or surface |

| | |
|----------------------------|------------------|
| Inlet Port | 1/8in female NPT |
| Outlet Port | 1/8in female NPT |
| Exhaust Port | 1/8in female NPT |
| Stackable | No |
| Flow Coefficient | 0.78 |
| Maximum Operating Pressure | 115 psi |
| Minimum Operating Pressure | 0 psi |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AVS-5271-HL.pdf>
See store item page for other formats.