

AVS-537D2-HL Cut Sheet



NITRA manual valve, 5-port (4-way), 2-position, handle, detented, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), Cv=1.39, panel or surface mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AVS-537D2-HL>

Technical Specifications

| | |
|---------------------|----------------------------|
| Brand | NITRA |
| Item | Valve |
| Working Fluid | Air |
| Valve Type | Manual directional control |
| Port Quantity | 5-port (4-way) |
| Number Of Positions | 2 |
| Operator Type | Handle |
| Action | Detented |
| Mounting | Panel or surface |
| Inlet Port | 1/4in female NPT |
| Outlet Port | 1/4in female NPT |
| Stackable | No |
| Flow Coefficient | 1.39 |
| Form Factor | Standard |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |