

# AWM20GY Cut Sheet



Atlas Wire AWM hook-up wire, single conductor, 20 AWG, 10-stranded, tinned copper, PVC conductor insulation material, gray, 300V, 500ft spool.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AWM20GY>

## Technical Specifications

<b>Brand</b>	Atlas Wire
<b>Item</b>	Wire
<b>Wire/Cable Type</b>	AWM
<b>UL Wire/Cable Type</b>	AWM
<b>Applicable Standards</b>	UL 758, UL 1569, UL 1007 and CSA C22.2 No. 210
<b>Application</b>	Hook-up
<b>Flexibility</b>	Flexible
<b>Voltage Rating</b>	300V
<b>Conductors</b>	Single conductor

<b>Conductor Size</b>	20 AWG
<b>Conductor Stranding</b>	10-stranded
<b>Conductor Material</b>	Tinned copper
<b>Conductor Insulation Material</b>	PVC
<b>Conductor Insulation Color</b>	Gray
<b>Nominal Overall Cable Diameter</b>	0.038in
<b>Bulk Length</b>	500ft spool

## Agency Approvals

<b>UL Listed File #</b>	E25635
<b>UL Recognized File #</b>	E25635
<b>UL Hazardous File #</b>	none
<b>CE</b>	None
<b>CSA File #</b>	150272
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>