

B121206SC Cut Sheet



Wiegmann enclosure, NEMA 12/13, 12 x 12 x 6in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/B121206SC>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Wiegmann |
| Item | Enclosure |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 12/13 |
| Nominal Enclosure Dimensions | 12 x 12 x 6in (HxWxD) |
| Enclosure Height | 12.31in |
| Enclosure Width | 12.31in |
| Enclosure Depth | 6.17in |
| Mounting | Wall |

| | |
|---------------------------------|--------------|
| Integral Mounting Feet | No |
| Integral Mounting Flange | Yes |
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Screw cover |
| Shelf | No |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|----------------------------------------|
| UL Listed File # | E23553 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/B121206SC.pdf>
See store item page for other formats.