

B424V30 Cut Sheet



Ashcroft mechanical pressure switch, 4.5 to 30 psig set point, 0.7 to 2.1 psig deadband range, Viton sensing element, Viton seal(s), SPDT 15A, 1/4in female NPT process connection, 3/4in female NPT conduit opening.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/B424V30>

Technical Specifications

Brand	Ashcroft
Item	Mechanical pressure switch
Media Type	Liquid, air, gases, oil, water and chemicals
Setpoint Range	4.5 to 30 psig
Deadband Range	0.7 to 2.1 psig
Wetted Parts	Viton, stainless steel
Sensing Element Material	Viton

Seal Material	Viton
Switching Output	SPDT 15A
Process Connection	1/4in female NPT
IP Rating	IP66
NEMA Rating	4X
Electrical Connection	3/4in female NPT conduit opening
Manufacturer Part Number	B424V30#

Agency Approvals

UL Listed File #	E34743
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	055528
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/B424V30.pdf>
See store item page for other formats.