

B424V60 Cut Sheet



Ashcroft mechanical pressure switch, 9 to 60 psig set point, 1.4 to 4.9 psig deadband range, Viton sensing element, Viton seal(s), SPDT 15A, 1/4in female NPT process connection, 3/4in female NPT conduit opening.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/B424V60>

Technical Specifications

Brand	Ashcroft
Item	Mechanical pressure switch
Media Type	Liquid, air, gases, oil, water and chemicals
Setpoint Range	9 to 60 psig
Deadband Range	1.4 to 4.9 psig
Wetted Parts	Viton, stainless steel
Sensing Element Material	Viton

Seal Material	Viton
Switching Output	SPDT 15A
Process Connection	1/4in female NPT
IP Rating	IP66
NEMA Rating	4X
Electrical Connection	3/4in female NPT conduit opening
Manufacturer Part Number	B424V60#

Agency Approvals

UL Listed File #	E34743
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	055528
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/B424V60.pdf>
See store item page for other formats.