

BB251615W Cut Sheet



AttaBox BantamBox series enclosure, NEMA 1/3R/4/4X/12, 250 x 160 x 150mm (HxWxD), polycarbonate, RAL 7035 light gray, screw cover, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BB251615W>

Technical Specifications

| | |
|---------------------------------|------------------------------|
| Brand | AttaBox |
| Item | Enclosure |
| Series | BantamBox |
| Subpanel | Purchase subpanel separately |
| NEMA Rating | 1/3R/4/4X/12 |
| IP Rating | IP66 |
| Enclosure Height | 250.00mm |
| Enclosure Width | 160.00mm |
| Enclosure Depth | 150.00mm |
| Cover Type | Screw cover |
| Cover Depth | 75mm |
| Integral Mounting Flange | No |
| Material | Polycarbonate |
| Color | RAL 7035 light gray |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E319779 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |