


# BBV1200-ADC Cut Sheet



Winters manual block and bleed needle valve, straight body soft seat, double handles, stainless steel body, 1/4in male NPT inlet(s), 1/4in female NPT outlet(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BBV1200-ADC>

## Technical Specifications

<b>Brand</b>	Winters
<b>Item</b>	Needle valve
<b>Valve Type</b>	Manual block and bleed
<b>Form Factor</b>	Straight body soft seat
<b>Operator Type</b>	Double handles
<b>Body Material</b>	Stainless steel
<b>Inlet Port</b>	1/4in male NPT
<b>Outlet Port</b>	1/4in female NPT
<b>Operating Pressure</b>	6,000 psi @ 212°F
<b>Operating Temperature</b>	32°F to 383°F (0°C to 195°C)

## Agency Approvals

<b>CE</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/BBV1200-ADC.pdf>  
See store item page for other formats.