

# BC18-25 Cut Sheet



Minerallac hammer-on beam clamp, 75 lbs. Package of 25. For use with 1/8 to 1/4in flanges and 1/4-20 threaded rod.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BC18-25>

## Technical Specifications

Brand	Minerallac
Item	Clamp
Clamp Type	Beam
Attachment Type	Hammer-on
Mounting Holes	1/4-20 UNC bottom and 1/4-20 UNC back
Load Rating	75 lbs
Material	Spring steel
Finish	Zinc phosphate plated
Minimum Flange Thickness	1/8in
Maximum Flange Thickness	1/4in
UL Type	UL 2239
Quantity per Pack	25
For Use With	1/8 to 1/4in flanges and 1/4-20 threaded rod

## Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>