

BC18KC112 Cut Sheet



Minerallac hammer-on beam clamp conduit hanger assembly, spring clip, bottom mount, 75 lbs, UL Type UL 2239. Package of 100. For use with 1/8 to 1/4in flanges and 1-1/2in conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BC18KC112>

Technical Specifications

Brand	Minerallac
Item	Conduit hanger assembly
Mount Type	Hammer-on beam clamp
Hanger Type	Spring clip
Mount Side	Bottom
Material	Spring steel
Finish	Zinc phosphate plated
Mounting Holes	1/4-20 UNC back
Minimum Flange Thickness	1/8in
Maximum Flange Thickness	1/4in
Load Rating	75 lbs
Outside Diameter	1.73in-1.91in

Rigid Metallic Conduit (RMC) Trade Size	1-1/2in
Electrical Metallic Tubing (EMT) Trade Size	1-1/2in
Intermediate Metallic Conduit (IMC) Trade Size	1-1/2in
Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1-1/2in
UL Type	UL 2239
Quantity per Pack	100
For Use With	1/8 to 1/4in flanges and 1-1/2in conduit

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document