

BC18KC114-10 Cut Sheet



Minerallac hammer-on beam clamp conduit hanger assembly, spring clip, bottom mount, 75 lbs, UL Type UL 2239. Package of 10. For use with 1/8 to 1/4in flanges and 1-1/4in conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BC18KC114-10>

Technical Specifications

Brand	Minerallac	Rigid Metallic Conduit (RMC) Trade Size	1-1/4in
Item	Conduit hanger assembly	Electrical Metallic Tubing (EMT) Trade Size	1-1/4in
Mount Type	Hammer-on beam clamp	Intermediate Metallic Conduit (IMC) Trade Size	1-1/4in
Hanger Type	Spring clip	Reduced Wall Flexible Metal Conduit Trade Size	1-1/4in
Mount Side	Bottom	Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1-1/4in
Material	Spring steel	UL Type	UL 2239
Finish	Zinc phosphate plated	Quantity per Pack	10
Mounting Holes	1/4-20 UNC back	For Use With	1/8 to 1/4in flanges and 1-1/4in conduit
Minimum Flange Thickness	1/8in		
Maximum Flange Thickness	1/4in		
Load Rating	75 lbs		
Outside Diameter	1.51in-1.66in		

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document