

BC916-25 Cut Sheet



Minerallac hammer-on beam clamp, 75 lbs. Package of 25. For use with 9/16 to 3/4in flanges and 1/4-20 threaded rod.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BC916-25>

Technical Specifications

Brand	Minerallac
Item	Clamp
Clamp Type	Beam
Attachment Type	Hammer-on
Mounting Holes	1/4-20 UNC bottom and 1/4-20 UNC back
Load Rating	75 lbs
Material	Spring steel
Finish	Zinc phosphate plated
Minimum Flange Thickness	9/16in
Maximum Flange Thickness	3/4in
UL Type	UL 2239
Quantity per Pack	25
For Use With	9/16 to 3/4in flanges and 1/4-20 threaded rod

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document